

# WM-442-ADA - Wall Mount Shower

The Pool Shower, Inc.  
Dallas, Georgia  
www.poolshower.com—1-866-shower1

*Manufacturers of Quality Stainless Steel Showers*



## PARTS LIST:

- ① DEL-78 2.5 GPM Chrome Plated Brass Shower Head
- ② SR-40 1/2" x 39" 304 sch 40 Stainless Steel Riser TBE
- ③ WB-2 2" Stainless Steel Wall Bracket & Flange  
Stainless Steel Phillips Oval Head Screws (2) - size #8, length: 1-1/2  
Stainless Steel Socket Point Type Set Screw Thread Size: 1/4-20
- ④ AV-ADA-442 Chrome Plated Brass Adjustable Self-closing Metered Push Valve - 1/2" NPT
- ⑤ WXF-2 2" Chrome Plated Brass Wall Trim Flange

Accessories may vary due to availability and slight modifications by the manufacturer.

## Installation Guidelines

- Recommended Shower Head Height: 78"
- Water Supply Line thread should be exposed through wall and roughed in at 40" - 41" from flooring surface.


1. Bring 1/2" water supply line out of wall at approximately 40" from flooring surface in order for shower head height to be at 78".
2. Slide mounting bracket onto riser.
3. Using a level or plumb line, mark placement holes for mounting bracket.
4. Attach shower riser to angle valve using Teflon tape on threads.
5. Connect water supply line to angle valve.
6. Pre-drill previously marked holes for placement of mounting brackets.
7. Secure unit to wall with stainless steel screws.
8. Tighten set screw on ring bracket.



- Riser: SR-44-120
- 120° Bend
- 2.5" Chrome Plated Brass Shower Head

- Riser: SR-44-90
- 90° Bend
- 90° Stainless Steel Elbow
- 6" Chrome Plated Brass Shower Head

- Riser: SR-44-90
- 90° Bend
- 90° Stainless Steel Elbow
- 6" Stainless Steel Shower Head



ROUNDING IN DIMENSIONS MAY VARY AND ARE SUBJECT TO CHANGE—NO RESPONSIBILITY IS ASSUMED FOR USE OF SUPERCEDED OR VOIDED DATA.



WWW.POOLSHOWER.COM  
1-866-SHOWER1

MODEL NUMBER:

WM-442-ADA

JOB NAME :

ITEM NO.


SUBMITTED AS SHOWN:

SUBMITTED AS NOTED :

SEE ATTACHED FOR SUBMITTED MODIFICATION :



SIDE VIEW



**TECHNICAL DATA:**

- EXPOSED WALL MOUNTED TWO VALVE SHOWER FITTING
- FINISH: CHROME PLATED BRASS
- 1/2" X 39" STAINLESS STEEL RISER TBE
- LEVER HANDLES
- 1/2" NPT FEMALE INLETS
- ADJUSTABLE SUPPLY ARMS
- 2.5 GPM SHOWER HEAD
- ASME A112.18.1M COMPLIANT
- CSA B125 COMPLIANT

DATE:

BY:

CHCKD:




APP'D:

REV:

# WM-442-ADA WALL MOUNT SHOWER UNIT



## ADA COMPLIANT METERED ANGLE VALVE ADJUSTABLE EXTERNAL TIMING: 1-20 SECONDS

- Time is changed by rotating plastic-serrated adjustment nut with a pair of pliers.
- Valve closes with water pressure
- Raising nut (counter clockwise) shortens time, lowering nut (clockwise) lengthens time.
- Once cycle time is satisfactory, lock handle in place making sure set screw is securely fastened on groove in stem.
- Replace button.



### HOW TO ADJUST

TOP VIEW




**NOTE:** Flush supply lines before installing valve to remove chips and dirt which can become lodged in the seat washer and cause the faucet to malfunction.

**WINTERIZING:** It is recommended that a shut-off valve be installed in the water line going to the pool shower connection where freezing temperatures can occur. Accessories can be removed and other parts partially disassembled for complete protection against freeze damage.

**FREEZE DAMAGE IS NOT COVERED BY THE WARRANTY.**


## OPTIONAL ACCESSORIES

### #AV-442-CHV CROSS HANDLE VALVE FOOT SHOWER



\*39" RISER IS REPLACED WITH 32" RISER WHEN DIVERTER IS USED.

### #PCV-2193 PULL CHAIN VALVE



### #HBA-158 HOSE BIBB WITH VACUUM BREAKER

